Fair-Rite Products Corp.

Your Signal Solution®

## Multi- Aperture cores (2873000202)



Part Number: 2873000202

73 MULTI- APERTURE CORE

Explanation of Part Numbers: – Digits 1 & 2 = Product Class – Digits 3 & 4 = Material Grade

 $\Box$  – Last digit 2 = Burnished

## Multi- aperture cores are used in suppression applications and in balun (balance- unbalance) and other broadband transformers. They are also employed in airbag designs to prevent accidental activation.

□All multi- aperture cores are supplied burnished.

Our "Multi- Aperture Core Kit" (part number 0199000036) is available for prototype evaluation.

For any multi- aperture requirement not listed here, feel free to contact our customer service group for availability and pricing.

Weight: 3.7 (g)

TT OIGHT	<u></u>			
Dim	mm	mm tol	nominal inch	inch misc.
А	13.3	±0.60	0.525	
В	14.35	±0.50	0.565	
C	7.5	±0.35	0.295	_
Е	5.7	±0.25	0.225	
H	3.8	±0.25	0.15	

Typical Impedance $(\Omega)$				
10 MHz	125			
$25 \text{ MHz}^+$	106			

Multi- aperture cores in 73 and 43 materials are controlled for impedance only. The 61 NiZn material is controlled for both impedance and  $A_L$  value. The high frequency 67 material is controlled for  $A_L$  value. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is typically the listed impedance less 20%.

□Multi- aperture cores in 73 and 43 material are measured for impedance on the 4193A Vector Impedance Analyzer. The 61 and 67 multi- aperture cores are tested on the 4291A Impedance Analyzer. All impedance measurements are performed with a single turn to both holes, using the shortest practical wire length.

 $\Box$  The 61 and 67 material multi- hole beads are tested for A<sub>L</sub> value. The test frequency is 10 kHz at < 10 gauss. The test winding is five turns wound through both holes.